



CCMW 09T308, KBN35M, Type: ME

Order data

Order number	265642 ME
GTIN	4960664543960
Item class	25H

Description
Version:

MEGACOAT-coated CBN inserts. MultiEdge; 2 cutting edges per insert.

Grade: KBN35M

Cutting edge version: ME

Cutting depth a_p : 0.05 - 0.5 mm

Feed f : 0.08 - 0.15 mm/rev.

Cutting speed v_c main application: 120 - 200 m/min

Technical description

Cutting conditions	continuous
Cutting speed v_c main application	120 - 200 m/min
Cutting edge version	ME
Cutting depth a_p	0.05 - 0.5 mm
Corner radius	0.8 mm
Feed f	0.08 - 0.15 mm/rev.

Grade	KBN35M
Finishing/roughing assignment	Finishing
Tool material	CBN
ISO code indexable insert	CCMW 09T308
Number of changes/inserts	2
Product name attribute	KBN35M
Type of product	Indexable insert for turning

User data

	Suitability	V_c	ISO code
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
irregular	suitable only under restricted conditions		
interrupted	suitable		
dry	suitable		