

Garant
Parting-off tool Steel, neutral, Blade height h₅ / groove width w: 26/4,1 mm

Order data

Order number	273551 26/4,1
GTIN	4045197698971
Item class	21W

Description
Suitable for :

Toolholder No. 273984 – 274000 or No. 319132; 319133 (VDI toolholder).

Supplied with:

Supplied with key No. 279850 1 for changing inserts.

axial grooving possible: no

for maximum workpiece Ø: 80 mm

Width b₂: 3.2 mm

Height h₁: 21.4 mm

Overall length L_{tot}: 110 mm

max. groove depth t_{max}: 40 mm

Technical description

Width b ₂	3.2 mm
for maximum workpiece Ø	80 mm
Groove width w	4.1 mm
Blade height h ₅	26 mm
Height h ₁	21.4 mm
Overall length L _{tot}	110 mm
max. groove depth t _{max}	40 mm
Application type	neutral
Through-coolant	no

axial grooving possible	no
Type of product	Parting-off tool