

Garant
Parting-off tool Steel, neutral, Blade height h₅ / groove width w: 32/3,1 mm


Order data

Order number	273551 32/3,1
GTIN	4045197699008
Item class	21W

Description

Suitable for :

Toolholder No. 273984 – 274000 or No. 319132; 319133 (VDI toolholder).

Supplied with:

Supplied with key No. 279850 1 for changing inserts.

axial grooving possible: no

for maximum workpiece Ø: 100 mm

Width b₂: 2.35 mm

Height h₁: 25 mm

Overall length L_{tot}: 150 mm

max. groove depth t_{max}: 50 mm

Technical description

Groove width w	3.1 mm
Blade height h ₅	32 mm
for maximum workpiece Ø	100 mm
Width b ₂	2.35 mm
Height h ₁	25 mm
Overall length L _{tot}	150 mm
max. groove depth t _{max}	50 mm
Application type	neutral
Through-coolant	no

axial grooving possible	no
Type of product	Parting-off tool