

Garant
Parting-off tool Steel, neutral, Blade height h₅ / groove width w: 19/2,2 mm


Order data

Order number	273551 19/2,2
GTIN	4045197698933
Item class	21W

Description

Suitable for :

Toolholder No. 273984 – 274000 or No. 319132; 319133 (VDI toolholder).

Supplied with:

Supplied with key No. 279850 1 for changing inserts.

axial grooving possible: no

for maximum workpiece Ø: 40 mm

Width b₂: 1.6 mm

Height h₁: 15.7 mm

Overall length L_{tot}: 86 mm

max. groove depth t_{max}: 20 mm

Technical description

Width b ₂	1.6 mm
Groove width w	2.2 mm
for maximum workpiece Ø	40 mm
Blade height h ₅	19 mm
Height h ₁	15.7 mm
Overall length L _{tot}	86 mm
max. groove depth t _{max}	20 mm
Application type	neutral
Through-coolant	no

axial grooving possible	no
Type of product	Parting-off tool