



Linishing machine GIS, Type: 790229



Order data

Order number	077612 790229
GTIN	2050001676740
Item class	03H

Description

Version:

GRIT GI linisher range for demanding industrial applications: **Sturdy design**, with **extremely powerful motors**.

- **High efficiency due to best removal rate.**
- **Powerful 4 kW motor (400 V, 3 ~, 50 Hz).**
- **Patented belt-tensioning system,**
- **High operational safety: Stop, linishing gap, and eye protection are individually adjustable.**

The ideal solution for all those who need a linishing machine only (i.e. without any expansion options). Sturdy compact design and easy operation ensure first-class results. Easily adjustable working height, chip collector.

Supplied with:

Machine base, CEE plug (16 A), 1 linishing belt 2000 mm; 36 grit.

Note:

For linishing belts see No. 558310 ff and No. 558453-56.

Technical description

Manufacturer's designation	GIS 75
Tape width	75 mm
Band length	2000 mm
Weight	74 kg
maximum speed	3000 min ⁻¹
Power supply	Mains operated
Type of product	Linishing machine

Accessories

Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 36	558453 36
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 80	558453 80
Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 40	558310 40
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 120	558453 120
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 60	558454 60
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 120	558454 120
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 60	558453 60
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 36	558454 36
Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit 80	558454 80
Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 120	558310 120
Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit 60	558310 60

Linishing belt zirconium aluminium oxide (ZA)ZK713X Grit
80

558310 80

Zirconium Aluminium Oxide (ZA) linishing beltGRIT R Grit
36

558456 36