

Garant
Parting-off tool Steel, neutral, Blade height h_5 / groove width w : 26/3,1 mm


Order data

Order number	273551 26/3,1
GTIN	4045197698964
Item class	21W

Description

Suitable for :

Toolholder No. 273984 – 274000 or No. 319132; 319133 (VDI toolholder).

Supplied with:

Supplied with key No. 279850 1 for changing inserts.

axial grooving possible: no

for maximum workpiece \varnothing : 75 mm

Width b_2 : 2.35 mm

Height h_1 : 21.4 mm

Overall length L_{tot} : 110 mm

max. groove depth t_{max} : 25 mm

Technical description

Groove width w	3.1 mm
Blade height h_5	26 mm
for maximum workpiece \varnothing	75 mm
Width b_2	2.35 mm
Height h_1	21.4 mm
Overall length L_{tot}	110 mm
max. groove depth t_{max}	25 mm
Application type	neutral
Through-coolant	no

axial grooving possible	no
Type of product	Parting-off tool