



## Short drill chuck Form A, SK 40, Clamping range: 0,5-13mm



### Order data

Order number	301490 0,5-13
GTIN	2050001690548
Item class	33W

### Description

**Version:**

For clockwise and anticlockwise rotation.

**Supplied with:**

Hexagon screwdriver with T-handle.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

Spare chuck key No. 627425	SW6
Overhang dimension A	90 mm
Clamping range	0.5 - 13 mm
External Ø D	50 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 30 µm
Type of product	Short drill chuck

---

**Accessories**

Set of chuck jaws 3 pieces for chuck range 0,5-13 mm	309701 0,5-13
Pinion for chuck range 0,5-13 mm	309702 0,5-13