

Garant
Grooving insert Full radius, CBN825, Groove width w: 6mm

Order data

Order number	273746 6
GTIN	4045197643636
Item class	21H

Technical description

Groove width w	6 mm
Tolerance groove width w	±0.03 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	CBN
Main application	H
Cutting conditions	continuous
Grade	CBN825
Number of changes/inserts	1
Indexable insert profile	neutral
Type of product	Indexable insert for grooving

User data

	Suitability	V _c	ISO code
--	-------------	----------------	----------

Steel < 55 HRC	suitable	100 m/min	H
Steel < 60 HRC	suitable	100 m/min	H
Steel < 67 HRC	suitable	100 m/min	H
continuous	suitable		
irregular	suitable only under restricted conditions		
dry	suitable		