

## Slotted reducing adapter sealed, Ø 20 mm, Clamping range Ø D1: 8mm



### Order data

Order number	302160 8
GTIN	4019208190839
Item class	33D

### Description

#### Version:

Sealed (rubber plug).

#### Application:

- For drilling, reaming, milling, and tool sharpening.
- Very high flexibility due to reduction in clamping diameter.
- High torque guarantees a greater metal removal rate than with direct clamping.
- Concentricity  $\pm 5 \mu\text{m}$  (system accuracy at  $3\times D$ ).
- Concentricity  $\pm 2 \mu\text{m}$  (for reducing adapter).
- Can be used in all commercially available hydraulic chucks.

#### Optional extras:

Parallel wipers No. 343720.

### Technical description

Clamping Ø D <sub>1</sub>	8 mm
Ø D	20 mm
External Ø	20 mm
Product name attribute	Ø 20 mm
Concentricity system	5 $\mu\text{m}$
Type of product	Reducing adapter

