

Slotted reducing adapter sealed, Ø 20 mm, Clamping range Ø D1: 10mm



Order data

Order number	302160 10
GTIN	4019208190846
Item class	33D

Description

Version:

Sealed (rubber plug).

Application:

- For drilling, reaming, milling, and tool sharpening.
- Very high flexibility due to reduction in clamping diameter.
- High torque guarantees a greater metal removal rate than with direct clamping.
- Concentricity $\pm 5 \mu\text{m}$ (system accuracy at $3\times D$).
- Concentricity $\pm 2 \mu\text{m}$ (for reducing adapter).
- Can be used in all commercially available hydraulic chucks.

Optional extras:

Parallel wipers No. 343720.

Technical description

Ø D	20 mm
Clamping Ø D ₁	10 mm
External Ø	20 mm
Product name attribute	Ø 20 mm
Concentricity system	5 μm
Type of product	Reducing adapter

