

Garant
Grooving toolholder, left-hand, Shank width / groove width w: 25/2,5mm

Order data

Order number	273756 25/2,5
GTIN	4045197485038
Item class	21W

Description
Version:

Made of high-tensile tool steel ($> 1300 \text{ N/mm}^2$). In conjunction with the convex insert clamping, the system achieves very high resistance to axial and radial cutting forces and thereby significantly increases the surface quality and productivity.

Note:

From groove width 6 mm at t_{\max} ($5 \times$ groove width), the second cutter comes into contact with the workpiece. This can lead to scoring. Reliably free of scoring up to $t = 24.5 \text{ mm}$.

Technical description

Grooving depth t_{\max}	12.5 mm
Screw	279815 6 (TX25; 6 Nm)
Functional width L_4	26.5 mm
Groove width w	2.5 mm
Head length L_1	33 mm
Overall length L	150 mm
Shank width b	25 mm
Application type	left-hand
Through-coolant	no
axial grooving possible	yes

Type of product	Boring bar
-----------------	------------

Accessories

Clamping screw Type 6	279815 6
8 mm blade with magnetwith 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25
Torque screwdriverwith scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600