

Garant
Grooving toolholder, right-hand, Shank / groove width w: 12/3mm

Order data

Order number	273750 12/3
GTIN	4045197484482
Item class	21W

Description
Version:

Made of high-tensile tool steel ($> 1300 \text{ N/mm}^2$). In conjunction with the convex insert clamping, the system achieves very high resistance to axial and radial cutting forces and thereby significantly increases the surface quality and productivity.

Technical description

Functional width L_4	12 mm
Groove width w	3 mm
Screw	279815 4 (TX15; 3.5 Nm)
Head length L_1	30 mm
Grooving depth t_{\max}	9 mm
Overall length L	150 mm
Shank width b	12 mm
Application type	right-hand
Through-coolant	no
axial grooving possible	yes
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Clamping screw Type 4	279815 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500