

**Cordless grinder AOS-B 32 mm 2.5 Ah stroke 3 mm, Type: AOS-B****Order data**

Order number	552436 AOS-B
GTIN	
Item class	07E

Description**Version:**

The energy-efficient Mirka® AOS-B 130 (oscillating) belongs to the family of small, brushless, battery-powered spot repair grinding machines. The powerful, cordless sander has an ergonomic design to ensure comfortable working over long periods. The operating time is up to 16 hours and the battery charging time is just 40 minutes. The Mirka® AOS-B 130 has a stroke of 3 mm.

Application:

grinding

Supplied with:

1 pc. charger, 1 pc. cable for the charger, 1 pc. replacement battery and 2 pcs. Quick Lock disc

Technical description

Number of rechargeable batteries contained	2
Speed range	4000 - 8000 min ⁻¹
Battery capacity	2.5 Ah
maximum polishing tool Ø	32
Weight	0.57 kg

Data sheet

Power supply	Battery-powered
maximum vibration to EN	2.54
Type of rechargeable battery	Lithium-ion
Battery voltage	12 V
Type of product	Polishing machine