

**Garant**

**"5 in 1" drilling and turning tool 2.25×D, right-hand, Ø DC: 20mm**


**Order data**

Order number	268467 20
GTIN	4045197470171
Item class	21X

**Description**
**Version:**

With internal cooling.

Plain shank **with collar**.

**Application:**

Face turning, longitudinal turning, drilling, internal longitudinal turning, countersinking.

**Note:**

- **Choose corner radii as large as possible.**
- **Always use internal cooling for drilling (at least 5 bar).**

Use the drilling and turning tool **in long chipping structural steels and long chipping stainless steels only up to 1.5×D.**

**Technical description**

Indexable insert No. 268472 – 268496	WCHX 10T3..
Pack of insert screws	269028 35
Bore Ø tolerance D	0/+0.33 mm
Nominal Ø D	20 mm
Shank Ø D <sub>s</sub>	25 mm
Shank length L <sub>s</sub>	56 mm
Reach L <sub>1</sub>	45 mm
Ø d <sub>2</sub>	32 mm

Overhang L <sub>A</sub>	56 mm
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 35	269028 35
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20	674248 TX20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500