

Garant
RC.X 1003, Grade: HB7120-1


Order data

Order number	260640 HB7120-1
GTIN	4045197818232
Item class	21G

Description

RC.X 1003 HB7120-1 Chip breaker: VM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Cutting depth a_p	0.5 - 2 mm
Chip breaker	VM
Feed f	0.1 - 0.3 mm/rev.
Grade	HB7120-1
Cutting speed v_c main application	80 - 260 m/min
Main application	M
Cutting conditions	continuous

Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	RCMX 1003
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning