

Garant**SC.T 09T304, Grade: HB7120-1**

Order data

Order number	260762 HB7120-1
GTIN	4045197818294
Item class	21G

Description

SC.T 09T304 HB7120-1 Corner radius: 0.4 mm

Grade: HB7120-1

Chip breaker: VM

Tolerance: M

Cutting depth a_p : 0.5 - 2.5 mm

Feed f : 0.1 - 0.4 mm/rev.

Technical description

Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.5 - 2.5 mm
Cutting speed v_c main application	80 - 260 m/min
Chip breaker	VM
Corner radius	0.4 mm
Grade	HB7120-1
Cutting conditions	continuous

Main application	M
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	SCMT 09T304
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning