

Garant
"5 in 1" drilling and turning tool 1.5×D, left-hand, Ø DC: 10mm

Order data

Order number	268464 10
GTIN	4045197470089
Item class	21X

Description
Version:

With internal cooling.

Plain shank.

Application:

Face turning, longitudinal turning, drilling, internal longitudinal turning, countersinking.

Note:

- **Choose corner radii as large as possible.**
- **Always use internal cooling for drilling (at least 5 bar).**

Technical description

Nominal Ø D	10 mm
Bore Ø tolerance D	0/+0.22 mm
Pack of insert screws	269028 31
Indexable insert No. 268472 – 268496	WCHX 05T1..
Shank Ø D _s	12 mm
Reach L ₁	15 mm
Overall length L	90 mm
Application type	left-hand
Through-coolant	yes
Type of product	Boring bar

Accessories

Set of insert screws Type 31	269028 31
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500