

Garant
VC.T 160404, Grade: HB7120-1


Order data

Order number	261458 HB7120-1
GTIN	4045197818928
Item class	21G

Description

VC.T 160404 HB7120-1 Grade: HB7120-1
 Chip breaker: VM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2.5 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Chip breaker	VM
Cutting conditions	continuous
Main application	M
Cutting speed v_c main application	80 - 260 m/min
Corner radius	0.4 mm
Feed f	0.1 - 0.4 mm/rev.

Grade	HB7120-1
Cutting depth a_p	0.5 - 2.5 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VCMT 160404
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning