

Garant
CC.T 120404, Grade: HB7140-1


Order data

Order number	260064 HB7140-1
GTIN	4045197818997
Item class	21G

Description

CC.T 120404 HB7140-1 Grade: HB7140-1
 Chip breaker: VS
 Tolerance: M
 Cutting depth a_p : 0.2 - 2.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 70 - 260 m/min

Technical description

Grade	HB7140-1
Feed f	0.1 - 0.3 mm/rev.
Main application	M
Corner radius	0.4 mm
Cutting speed v_c main application	70 - 260 m/min
Cutting conditions	slightly interrupted
Cutting depth a_p	0.2 - 2.5 mm

Chip breaker	VS
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 120404
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning