

**Garant**
**CC.T 120404, Grade: HB7140-1**


### Order data

Order number	260158 HB7140-1
GTIN	4045197819062
Item class	21G

### Description

CC.T 120404 HB7140-1 Grade: HB7140-1  
 Chip breaker: VM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.2 - 4 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 60 - 230 m/min

### Technical description

Chip breaker	VM
Grade	HB7140-1
Cutting depth $a_p$	0.2 - 4 mm
Main application	M
Corner radius	0.4 mm
Feed $f$	0.1 - 0.3 mm/rev.
Cutting speed $v_c$ main application	60 - 230 m/min

Cutting conditions	slightly interrupted
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	CCMT 120404
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning