

Garant
SCMT 09T304, Grade: HB7140-1


Order data

Order number	260742 HB7140-1
GTIN	4045197819208
Item class	21G

Description

SCMT 09T304 HB7140-1 Corner radius: 0.4 mm
 Grade: HB7140-1
 Chip breaker: VS
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 70 - 260 m/min

Technical description

Grade	HB7140-1
Main application	M
Chip breaker	VS
Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	70 - 260 m/min
Cutting conditions	slightly interrupted
Corner radius	0.4 mm

Feed f	0.1 - 0.3 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	SCMT 09T304
Number of changes/inserts	4
Type of product	Indexable insert for turning