

Garant**WCHX 060202, Type: SM**

Order data

Order number	268480 SM
GTIN	4045197470546
Item class	21K

Description

Suitable for:

Boring tool No. 268463 – 268468, size 11.

Technical description

Cutting speed v_c main application	110 - 220 m/min
Main application	P
Cutting speed v_c secondary application	110 - 140 m/min
Type	SM
Corner radius	0.4 mm
Secondary application	M
Grade	HB7120
Tool material	Carbide
ISO code indexable insert	WCHX 060202
Number of changes/inserts	3

suitable for tool dia. D_c	11 mm
Type of product	Indexable insert for turning