

Garant**Calipers, Measuring range: 150mm****Order data**

Order number	GG4101 150
GTIN	4069515051316
Item class	GGN

Description**Version:**

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Ergonomically optimised caliper. Error-free reading from colour-contrast scale.

Precision lapped measuring faces. Better reading due to a colour-contrast scale.

Supplied with:

5 pcs. analogue caliper No. 410100 150.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Graduation	1/128 in
Jaw length	40 mm
Measurement deviation E MPE	±0.05 mm
Standard	ISO 13385
Calibration	A1
Packaging	Wallet

Data sheet

Graduation	1/20 mm
Depth gauge	rectangular 3.7×1.3
Reversible reading	mm / inch
Measuring range	0 - 150 mm
Scale divisions	5 mm
Depth gauge available	yes
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal caliper

Suitable products

No Shop URL available for: GG4101 150