



Sealing ring HP for ER clamping nut CENTRO P, DI32, Clamping Ø (1 mm increments): 10mm



Order data

Order number	309668 10
GTIN	2050001705273
Item class	34F

Description

Version:

Mini = all sizes with "M", extremely slim design.

MiniSlim = sizes with "MS", extremely super slim design.

Taper = all sizes with "C".

Standard = all other sizes.

Vulcanised **high-pressure sealing rings** up to 80 bar.

0.5 mm clamping dia. range (+ 0.4 / - 0.1).

Suitable for:

ER CP clamping nuts No. 309665 size 32DI.

Note:

FAHRION system ER clamping nuts type CP and sealing rings type HP **do not fit on to other systems!**

FAHRION ER clamping nut CENTRO P HDC not suitable for standard ER collet chucks CENTRO P.

· **Sealing rings in 0.5 mm increments on request.**

· **Sealing rings DI40 on request.**

Not compatible with other sealing ring systems!

Technical description

Clamping Ø	10 mm
------------	-------

Series	Centro P
for type	D132
External Ø D	26.2 mm
Height L	2 mm
Type of product	Collet chuck accessories