

Garant**WCHX 070304, Type: ALU**

Order data

| | |
|--------------|---------------|
| Order number | 268484 ALU |
| GTIN | 4045197470645 |
| Item class | 21K |

Description

Suitable for:

Boring tool No. 268463 – 268468, size 15.

Technical description

| | |
|---|-----------------|
| Main application | N |
| Cutting speed v_c main application | 300 - 600 m/min |
| Corner radius | 0.4 mm |
| Secondary application | K |
| Cutting speed v_c secondary application | 180 m/min |
| Type | ALU |
| Grade | HU70AL |
| Tool material | Carbide |
| ISO code indexable insert | WCHX 070304 |
| Number of changes/inserts | 3 |

suitable for tool dia. D_c

15 mm

Type of product

Indexable insert for turning