

Garant**OZ clamping nut, Clamping chuck clamping range: 2-16mm****Order data**

Order number	309670 2-16
GTIN	4045197292155
Item class	31Z

Description**Version:**

- Nut is case-hardened and ground all around.
- With ball-bearing thrust collar for higher clamping forces and improved radial run-out characteristics.

Suitable for:

OZ collet chuck No. 300695; 302460; 302462; 302475 and No. 302477.

Technical description

Overall length L	24 mm
Clamping chuck clamping range	2 - 16 mm
maximum tightening torque	100 Nm
Thread	M33×1.5
External Ø D	43 mm
Standard	DIN 6388 D

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Type of product	Clamping nut

Accessories

C-hook (pin) spanner with square pin for external nut Ø 40/42 mm	628400 40/42
--	--------------