

**Garant****OZ clamping nut, Clamping chuck clamping range: 2-25mm****Order data**

Order number	309670 2-25
GTIN	4045197292162
Item class	31Z

**Description****Version:**

- Nut is case-hardened and ground all around.
- With ball-bearing thrust collar for higher clamping forces and improved radial run-out characteristics.

**Suitable for:**

OZ collet chuck No. 300695; 302460; 302462; 302475 and No. 302477.

**Technical description**

Overall length L	30 mm
Thread	M48x2
maximum tightening torque	180 Nm
Clamping chuck clamping range	2 - 25 mm
External Ø D	60 mm
Standard	DIN 6388 D

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Type of product	Clamping nut

---

## Accessories

C-hook (pin) spanner with square pin for external nut Ø 58/62 mm	628400 58/62
--	--------------