

**Garant****OZ clamping nut, Clamping chuck clamping range: 4-32mm****Order data**

Order number	309670 4-32
GTIN	4045197292179
Item class	31Z

**Description****Version:**

- **Nut is case-hardened and ground all around.**
- **With ball-bearing thrust collar for higher clamping forces and improved radial run-out characteristics.**

**Suitable for:**

OZ collet chuck No. 300695; 302460; 302462; 302475 and No. 302477.

**Technical description**

Overall length L	33.5 mm
maximum tightening torque	220 Nm
Thread	M60×2.5
Clamping chuck clamping range	4 - 32 mm
External Ø D	72 mm
Standard	DIN 6388 D

Balance quality G at rotational speed

G 2.5 at 25,000 rpm

Type of product

Clamping nut