



Clamping head smooth, SK 80, Clamping \varnothing (1 mm increments): 11 mm



Order data

Order number	329940 11
GTIN	2050001922755
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Smooth version for precision machining.

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping \varnothing	11 mm
Clamping face	smooth
Profile	round
Hardness	60 HR
Length L	53 mm

Version	shortened fittings
Adapter	SK 80
Type of product	Clamping head