

**Clamping head soft, SK 65, Initial bore Ø: 5mm****Order data**

Order number	329936 5
GTIN	2050001922656
Item class	33H

**Description****Version:**

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

**Application:**

Versatile application range, machining centres, measuring machines or pallet clamping.

**Note:**

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes, shapes (e.g. square) and machinable blanks **on request!**

**Technical description**

Initial bore Ø	5 mm
Hardness	60 HR
Profile	round
Length L	58 mm
Adapter	SK 65

Type of product

Clamping head