



Clamping head soft, SK 65, Initial bore Ø: 40mm



Order data

Order number	329936 40
GTIN	2050001922687
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes, shapes (e.g. square) and machinable blanks **on request!**

Technical description

Initial bore Ø	40 mm
Adapter	SK 65
Type of product	Clamping head

