

HAINBUCH
Clamping head with transverse serrations., SK 80, Clamping \varnothing (1 mm increments): 10 mm


Order data

| | |
|--------------|---------------|
| Order number | 329942 10 |
| GTIN | 2050001923479 |
| Item class | 33H |

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

With transverse serrations for raw material, small \varnothing .

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

| | |
|------------------------|-----------------------|
| Clamping \varnothing | 10 mm |
| Hardness | 60 HR |
| Clamping face | Transverse serrations |
| Profile | round |

| | |
|-----------------|---------------|
| Length L | 53 mm |
| Adapter | SK 80 |
| Type of product | Clamping head |