

**Clamping head smooth, SK 80, Clamping  $\varnothing$  (1 mm increments): 63mm****Order data**

Order number	329940 63
GTIN	2050001923271
Item class	33H

**Description****Version:**

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

Smooth version for precision machining.

**Application:**

Versatile application range, machining centres, measuring machines or pallet clamping.

**Note:**

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

**Technical description**

Clamping $\varnothing$	63 mm
Clamping face	smooth
Profile	round
Hardness	60 HR
Length L	53 mm

Version	shortened fittings
Adapter	SK 80
Type of product	Clamping head