

**Clamping head smooth, SK 80, Clamping  $\varnothing$  (1 mm increments): 15mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 329940 15     |
| GTIN         | 2050001922793 |
| Item class   | 33H           |

**Description****Version:**

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping  $\varnothing$  with order.**

Smooth version for precision machining.

**Application:**

Versatile application range, machining centres, measuring machines or pallet clamping.

**Note:**

**Clamping heads for special profiles to your individual requirements on request.**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

**Technical description**

|                        |        |
|------------------------|--------|
| Clamping $\varnothing$ | 15 mm  |
| Clamping face          | smooth |
| Profile                | round  |
| Hardness               | 60 HR  |
| Length L               | 53 mm  |

|                 |                    |
|-----------------|--------------------|
| Version         | shortened fittings |
| Adapter         | SK 80              |
| Type of product | Clamping head      |