

**WB quick-change holder internal machining, Type / Internal Ø R: 1/30mm****Order data**

Order number	316200 1/30
GTIN	4045197318787
Item class	33P

**Description****Application:**

To accept **Morse taper sleeves**, slotted sleeves and for **direct fitting of large boring bars** (type WB).

**Technical description**

Internal Ø R	30 mm
Type of product	Steel toolholder

**Accessories**

Clamping sleeve for plain shank Type / Clamping Ø 1/16 mm	316260 1/16
Clamping sleeve for plain shank Type / Clamping Ø 1/20 mm	316260 1/20

Clamping sleeve for plain shank Type / Clamping  $\varnothing$  1/25 mm

316260 1/25

Clamping sleeve for plain shank Type / Clamping  $\varnothing$  1/15 mm

316260 1/15

Clamping sleeve for plain shank Type / Clamping  $\varnothing$  1/12 mm

316260 1/12

Clamping sleeve for plain shank Type / Clamping  $\varnothing$  1/10 mm

316260 1/10