

**Clamping head smooth, SK 80, Clamping \varnothing (1 mm increments): 78mm****Order data**

| | |
|--------------|---------------|
| Order number | 329940 78 |
| GTIN | 2050001923424 |
| Item class | 33H |

Description**Version:**

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Smooth version for precision machining.

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

| | |
|------------------------|--------|
| Clamping \varnothing | 78 mm |
| Hardness | 60 HR |
| Profile | round |
| Clamping face | smooth |
| Length L | 53 mm |

| | |
|-----------------|--------------------|
| Version | shortened fittings |
| Adapter | SK 80 |
| Type of product | Clamping head |