

**Clamping head smooth, SK 80, Clamping \varnothing (1 mm increments): 38mm****Order data**

Order number	329940 38
GTIN	2050001923028
Item class	33H

Description**Version:**

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping \varnothing with order.**

Smooth version for precision machining.

Application:

Versatile application range, machining centres, measuring machines or pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping \varnothing	38 mm
Profile	round
Hardness	60 HR
Clamping face	smooth
Length L	53 mm

Version	shortened fittings
Adapter	SK 80
Type of product	Clamping head