



Clamping head with transverse and longitudinal serrations., SK 80, Clamping Ø (1 mm increments): 25mm



Order data

Order number	329944 25
GTIN	2050001923622
Item class	33H

Description

Version:

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify required clamping Ø with order.**

With transverse and longitudinal serrations for raw material.

Application:

Versatile application range: machining centres, measuring machines, and pallet clamping.

Note:

Clamping heads for special profiles to your individual requirements on request.

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

Technical description

Clamping Ø	25 mm
Hardness	60 HR
Profile	round
Clamping face	Transverse and longitudinal serrations

Length L	53 mm
Adapter	SK 80
Type of product	Clamping head