



WB quick-change holder internal machining, Type / Internal Ø R: 2/40mm



Order data

Order number	316200 2/40
GTIN	4045197318794
Item class	33P

Description

Application:

To accept **Morse taper sleeves**, slotted sleeves **and** for **direct fitting of large boring bars** (type WB).

Technical description

Internal Ø R	40 mm
Type of product	Steel toolholder

Accessories

Clamping sleeveFor MT shank Type 2/4	316240 2/4
Clamping sleevefor plain shank Type / Clamping Ø 2/10 mm	316260 2/10

Clamping sleeve for plain shank Type / Clamping Ø 2/15 mm	316260 2/15
Clamping sleeve For MT shank Type 2/3	316240 2/3
Clamping sleeve for plain shank Type / Clamping Ø 2/12 mm	316260 2/12
Clamping sleeve for plain shank Type / Clamping Ø 2/16 mm	316260 2/16
Clamping sleeve for plain shank Type / Clamping Ø 2/32 mm	316260 2/32
Clamping sleeve for plain shank Type / Clamping Ø 2/20 mm	316260 2/20
Clamping sleeve for plain shank Type / Clamping Ø 2/25 mm	316260 2/25