

**WB quick-change holder internal machining, Type / Internal Ø R: 3/40mm****Order data**

Order number	316200 3/40
GTIN	4045197318800
Item class	33P

**Description****Application:**

To accept **Morse taper sleeves**, slotted sleeves and for **direct fitting of large boring bars** (type WB).

**Technical description**

Internal Ø R	40 mm
Type of product	Steel toolholder

**Accessories**

Clamping sleeve for plain shank Type / Clamping Ø 2/20 mm	316260 2/20
Clamping sleeve for plain shank Type / Clamping Ø 2/25 mm	316260 2/25

Clamping sleeveFor MT shank Type 2/3	316240 2/3
Clamping sleevefor plain shank Type / Clamping Ø 2/10 mm	316260 2/10
Clamping sleevefor plain shank Type / Clamping Ø 2/16 mm	316260 2/16
Clamping sleevefor plain shank Type / Clamping Ø 2/12 mm	316260 2/12
Clamping sleeveFor MT shank Type 2/4	316240 2/4
Clamping sleevefor plain shank Type / Clamping Ø 2/15 mm	316260 2/15
Clamping sleevefor plain shank Type / Clamping Ø 2/32 mm	316260 2/32