



## WB quick-change holder internal machining, Type / Internal Ø R: 3/50mm



### Order data

Order number	316200 3/50
GTIN	4045197318817
Item class	33P

### Description

#### Application:

To accept **Morse taper sleeves**, slotted sleeves and for **direct fitting of large boring bars** (type WB).

### Technical description

Internal Ø R	50 mm
Type of product	Steel toolholder

### Accessories

Clamping sleeve for plain shank Type / Clamping Ø 3/25 mm	316260 3/25
Clamping sleeve for plain shank Type / Clamping Ø 3/20 mm	316260 3/20

Clamping sleeve for plain shank Type / Clamping Ø 3/32 mm	316260 3/32
Clamping sleeve For MT shank Type 3/3	316240 3/3
Clamping sleeve for plain shank Type / Clamping Ø 3/40 mm	316260 3/40
Clamping sleeve For MT shank Type 3/4	316240 3/4