



Short taper chuck flange DIN 55027, Ø d1 / taper: 160/5mm



Order data

Order number	317500 160/5
GTIN	4019208078656
Item class	33R

Description

Version:

Finish machined on all sides.

Application:

For retrofitting to lathe chucks with recessed mount to DIN 6350 A. **Lathe chucks with incorporated short tapers are preferable due to shorter overhang.**

For spindle noses **DIN 55027** and ISO 702/III (equals the old standard **DIN 55022**) with studs and collar nuts.

Material:

C45 steel

Technical description

Thickness B	21 mm
Taper Ø d ₂	82.575 mm
Taper size	5
Number of studs	4

External $\varnothing d_1$	160 mm
Type of product	Lathe chuck accessories