

**Garant**
**Shrink-fit chuck, HSK-A 40, Clamping range  $\varnothing$  D1: 8mm**

**Order data**

Order number	307950 8
GTIN	4045197376879
Item class	31A

**Description**
**Version:**

- **High-temperature steel.**
- **Integral tool length adjustment, adjustment track 10 mm.**
- **Sizes 3 – 5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID/Balluffchip bore.**

**GARANT:** - HSK mating faces machined.

**Application:**

For holding end mills and drills with parallel shank to h 6 tolerance. Suitable for inductive, contact and hot air shrink-fitting units.

**Optional extras:**

Coolant feed pipe No. 309880. Plug-in socket No. 309890. Shrink-fit chuck extension No. 302410 – 302416. Shrink-fit units No. 354210 – 304755.

**Technical description**

$\varnothing$ D <sub>2</sub>	21 mm
Clamping $\varnothing$ D <sub>1</sub>	8 mm
Overhang dimension A	80 mm
External $\varnothing$ D	27 mm
Adapter	HSK-A 40
Arbor standard	DIN 69893

Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Shrink-fit chuck

## Accessories

Cooling unit Type CU1	354215 CU1
Shrink-fit unit Type SU1	354210 SU1
Subframe cupboard	354290
Screening plate for coilSU1 for clamping $\varnothing$ 6-12 mm	354240 6-12
Cooling adapter long4.5° for clamping $\varnothing$ 6-9 mm	354236 6-9
Cooling adapter short4.5° for clamping $\varnothing$ 6-9 mm	354235 6-9