



Short drill chuck Form A, HSK-A 63, Clamping range: 0,3-8mm



Order data

Order number	307730 0,3-8
GTIN	2050001690012
Item class	33W

Description

Version:

- For clockwise and anticlockwise rotation.
- With RFID/Balluffchip bore.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

Technical description

Spare chuck key No. 627425	SW 4
Clamping range	0.3 - 8 mm
Type	standard
Overhang dimension A	96 mm
External Ø D	36 mm
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7
Arbor standard	DIN 69893-1
Shape	A

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 30 \mu\text{m}$
maximum tightening torque $M_{d \max}$	$\leq 14 \text{ Nm}$
Type of product	Short drill chuck

Accessories

Hexagon screwdriver, with T-handle Hexagon 4 mm	627481 4
---	----------