

**Short taper chuck flange DIN 55027, Ø d1 / taper: 200/6mm****Order data**

Order number	317500 200/6
GTIN	4019208078687
Item class	33R

**Description****Version:**

Finish machined on all sides.

**Application:**

**For retrofitting** to lathe chucks with recessed mount to DIN 6350 A. **Lathe chucks with incorporated short tapers are preferable due to shorter overhang.**

For spindle noses **DIN 55027** and ISO 702/III (equals the old standard **DIN 55022**) with studs and collar nuts.

**Material:**

C45 steel

**Technical description**

Number of studs	4
Taper Ø d <sub>2</sub>	106.39 mm
External Ø d <sub>1</sub>	200 mm
Taper size	6

Thickness B	23 mm
Type of product	Lathe chuck accessories