



Short taper chuck flange DIN 55027, Ø d1 / taper: 250/6mm



Order data

Order number	317500 250/6
GTIN	4019208078717
Item class	33R

Description

Version:

Finish machined on all sides.

Application:

For retrofitting to lathe chucks with recessed mount to DIN 6350 A. **Lathe chucks with incorporated short tapers are preferable due to shorter overhang.**

For spindle noses **DIN 55027** and ISO 702/III (equals the old standard **DIN 55022**) with studs and collar nuts.

Material:

C45 steel

Technical description

Taper Ø d ₂	106.39 mm
Number of studs	4
Thickness B	23 mm
Taper size	6

External $\varnothing d_1$	250 mm
Type of product	Lathe chuck accessories