



Short drill chuck Form A, HSK-A 63, Clamping range: 2,5-16mm



Order data

Order number	307730 2,5-16
GTIN	2050001690036
Item class	33W

Description

Version:

- For clockwise and anticlockwise rotation.
- With RFID/Balluffchip bore.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

Technical description

Spare chuck key No. 627425	6 AF
Type	standard
Overhang dimension A	109 mm
Clamping range	2.5 - 16 mm
External Ø D	57 mm
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7
Arbor standard	DIN 69893-1
Shape	A

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 30 μm
maximum tightening torque $M_{d\max}$	≤ 14 Nm
Type of product	Short drill chuck

Accessories

Hexagon screwdriver, with T-handle Hexagon 6 mm	627481 6
---	----------