



Flange blank for geared scroll chuck, External Ø D: 92 mm



Order data

Order number	317000 92
GTIN	4019208002941
Item class	33R

Description

Version:

Cleanly cast, unmachined, shot blasted, large allowance.

Application:

Attachment of **chucks with recessed mount to DIN 6350 to spindle noses DIN 800**. The adaptor plate blank must be machined and fitted to the machine and chuck.

Material:

Cast iron

Suitable for :

Three-jaw lathe chuck No. 310100; 310500, four-jaw lathe chuck **No. 312000; 312500** and combi lathe chuck **No. 315630**.

suitable for chuck Ø: 80 mm

Collar Ø d₂: 56 mm

Bore Ø d₃: 20 mm

Height h₁: 47 mm

Flange thickness h₂: 15 mm

Technical description

Bore Ø d ₃	20 mm
-----------------------	-------

External \varnothing D	92 mm
suitable for chuck \varnothing	80 mm
Collar \varnothing d ₂	56 mm
Height h ₁	47 mm
Flange thickness h ₂	15 mm
Type of product	Lathe chuck accessories