



Short taper chuck flange DIN 55027, Ø d1 / taper: 315/6mm



Order data

Order number	317500 315/6
GTIN	4019208033532
Item class	33R

Description

Version:

Finish machined on all sides.

Application:

For retrofitting to lathe chucks with recessed mount to DIN 6350 A. **Lathe chucks with incorporated short tapers are preferable due to shorter overhang.**

For spindle noses **DIN 55027** and ISO 702/III (equals the old standard **DIN 55022**) with studs and collar nuts.

Material:

C45 steel

Technical description

Taper Ø d ₂	106.39 mm
Thickness B	26 mm
External Ø d ₁	315 mm
Number of studs	4

Taper size	6
Type of product	Lathe chuck accessories