



## Flange blank for geared scroll chuck, External Ø D: 120 mm



### Order data

Order number	317000 120
GTIN	4019208002958
Item class	33R

### Description

#### Version:

Cleanly cast, unmachined, shot blasted, large allowance.

#### Application:

Attachment of **chucks with recessed mount to DIN 6350 to spindle noses DIN 800**. The adaptor plate blank must be machined and fitted to the machine and chuck.

#### Material:

Cast iron

#### Suitable for :

**Three-jaw lathe chuck No. 310100; 310500**, four-jaw lathe chuck **No. 312000; 312500** and combi lathe chuck **No. 315630**.

suitable for chuck Ø: 100 mm

Collar Ø d<sub>2</sub>: 80 mm

Bore Ø d<sub>3</sub>: 25 mm

Height h<sub>1</sub>: 58 mm

Flange thickness h<sub>2</sub>: 20 mm

### Technical description

suitable for chuck Ø	100 mm
----------------------	--------

Bore $\varnothing d_3$	25 mm
External $\varnothing D$	120 mm
Collar $\varnothing d_2$	80 mm
Height $h_1$	58 mm
Flange thickness $h_2$	20 mm
Type of product	Lathe chuck accessories